



## Bolt cutter, overall length: 460mm



### Order data

Order number	733300 460
GTIN	4003773066750
Item class	73F

### Description

#### Version:

Cutter head with compound action and universal jaws. Eccentric screws allow precise and easy adjustment of the blades. Forged centre stop with protective pads; powder-coated tubular handles with multi-component grips.

#### Application:

For cutting normal and high-tensile steels up to 48 HRC (about 1600 N/mm<sup>2</sup> tensile strength).

#### Material:

Head of chrome-vanadium high performance steel, cutting edges additionally induction hardened (approx. 62 HRC).

#### Spare part:

Spare jaws No. 733350.

### Technical description

for round steel bar up to 19 HRC and 800 N/mm <sup>2</sup> up to Ø	8 mm
for round steel bar up to 48 HRC and 1600 N/mm <sup>2</sup> up to Ø	5 mm
overall length	460 mm
for round steel bar up to 40 HRC and 1200 N/mm <sup>2</sup> up to Ø	6 mm
Material	Chrome vanadium high-performance steel
Type of product	Cutting pliers

---

## Accessories

Spare jaws complete with screws overall length 460 mm

733350 460