

LINDSTRÖM

Electronics side cutter, pointed head, SFW, overall length: 110mm**Order data**

Order number	726340 110
GTIN	7314150051045
Item class	73M

Description**Version:**

Slim shape with precision ground induction hardened cutting edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips made of conductive material with opening spring.

Suitable for ESDs. Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Technical description

overall length	110 mm
Head width	10 mm
Cutting capacity copper wire up to \varnothing	0.1 - 1.25 mm
Cutter length	10 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	very fine bevel
Material	High-performance steel alloy
Head shape	pointed
Handle	Plastic covering

Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Surface	black burnished
Product name attribute	SFW
with return spring	yes
Type of product	Cutting pliers