

LINDSTRÖM

Electronics side cutter, oval head, kW, overall length: 108mm**Order data**

Order number	726280 108
GTIN	7314150050932
Item class	73M

Description**Version:**

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs.** Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Technical description

Head width	8 mm
overall length	108 mm
Cutting capacity copper wire up to Ø	0.1 - 0.8 mm
Cutter length	8 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	High-performance steel alloy
Head shape	oval
Handle	Plastic covering

Manufacturing process	induction hardened cutting edges (63 – 65 HRC)
Surface	black burnished
Product name attribute	kW
with return spring	yes
Type of product	Cutting pliers