



Electronics oblique end cutter with long hollowed jaws, SFW, overall length: 118 mm



Order data

Order number	726880 118
GTIN	7314150051427
Item class	73M

Description

Version:

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs**. Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Cutting chamfer: very fine bevel

Head length: 18 mm

Head width: 10 mm

Cutting capacity copper wire up to \varnothing : 0.2 - 0.8 mm

Technical description

Head width	10 mm
overall length	118 mm
Cutting capacity copper wire up to \varnothing	0.2 - 0.8 mm
Head length	18 mm
electrical insulation	EGB/ESD
Cutting chamfer	very fine bevel
Joint	adjustable

Type of jaws	long, hollowed
Handle	Plastic grips
Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Material	High-performance steel alloy
Surface	black burnished
Product name attribute	SFW
with return spring	yes
Type of product	Cutting pliers