



Dungarees Quality Dress, pale grey, Clothing size DE: 48



Order data

Order number	091132 48
GTIN	4014382988692
Item class	09S

Description

Version:

Quality Dress workwear, 100 % cotton fabric. Cotton is especially resistant to chemical and mechanical influences and also to heat. Cotton is a natural product which is comfortable to wear due to its temperature-regulating properties and high absorbency.

Dungarees with 6 cm waistband adjustment.

- **Sewn-on raised kidney protection.**
- **Open bib patch pocket with hook and loop sub-division.**
- **Double bib with zip fastener pocket.**
- **Impact resistant and heat-resistant plastic buckle.**

Description:

- **Zip fastener in the flies.**
- **Two reinforced front patch pockets.**
- **Thigh pocket.**
- **Mobile phone patch pocket.**
- **Reinforced knee area.**
- **Ruler pocket.**

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Available in other colours on request.

Dungarees in cornflower blue under No. 091131.

Fabric composition: 100% cotton

Material weight/fabric density: 285 g/m²

Clothing standard: UV standard 801

Washing: 60 °C coloureds

Technical description

Unisex size	M
Number of metre rule pockets	1
Clothing size DE	48
double bib with zip fastener pocket.	yes
Trouser flies	Zip fastener
Side pockets	patch, reinforced
Bib pocket	patch, with hook and loop sub-division
reinforced knee area	yes
Number of knee pockets	2
Number of thigh pockets	1
Trouser leg end form	straight, open
Mobile phone pocket	yes
Plug cap	impact-resistant and heat-resistant plastic buckle
Number of side pockets	2
Kidney protection	yes
Material	Cotton
Size FR	42
Size UK	32R
Size US	33/31
Size IT	42
Series	QUALITY DRESS
Special service provision	Textile finishing

Size NL	48
Size ES	42
Gender	Gentlemen's
Fabric composition	100% cotton
Material weight/fabric density	285 g/m ²
Clothing standard	UV standard 801
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Colour	pale grey
Type of product	Dungarees