

VBW

UNIBOLT® bolt cutter, overall length: 460mm



Order data

| | |
|--------------|---------------|
| Order number | 733500 460 |
| GTIN | 4005887563200 |
| Item class | 73L |

Description

Version:

Cutter head with compound action and universal jaws. Eccentric screws allow precise and easy adjustment of the blades. Drop forged, centre stop with extra-large shock-absorbing zone; painted tubular handles.

Application:

For cutting normal and high-tensile steels up to 48 HRC (about 1600 N/mm² tensile strength).

Material:

Special tool steel jaws, blades induction hardened.

Spare part:

Spare jaws No. 734110.

Technical description

| | |
|---|--------------------|
| for round steel bar up to 40 HRC and 1200 N/mm ² up to Ø | 6 mm |
| overall length | 460 mm |
| for round steel bar up to 19 HRC and 800 N/mm ² up to Ø | 8 mm |
| for round steel bar up to 48 HRC and 1600 N/mm ² up to Ø | 5 mm |
| Cutting capacity | <48 HR |
| with over-expansion guard | yes |
| Manufacturer's designation | UNIBOLT® |
| Blade | hardened |
| Material | Special tool steel |

| | |
|-----------------------|----------------|
| Surface | Painted red |
| with adjustment screw | yes |
| Type of product | Cutting pliers |

Accessories

| | |
|---|------------|
| Spare jaws complete with screws overall length 460 mm | 734110 460 |
|---|------------|