

VBW

UNIBOLT® bolt cutter, overall length: 910mm



Order data

Order number	733500 910
GTIN	4005887563507
Item class	73L

Description

Version:

Cutter head with compound action and universal jaws. Eccentric screws allow precise and easy adjustment of the blades. Drop forged, centre stop with extra-large shock-absorbing zone; painted tubular handles.

Application:

For cutting normal and high-tensile steels up to 48 HRC (about 1600 N/mm² tensile strength).

Material:

Special tool steel jaws, blades induction hardened.

Spare part:

Spare jaws No. 734110.

Technical description

for round steel bar up to 19 HRC and 800 N/mm ² up to Ø	13 mm
overall length	910 mm
for round steel bar up to 48 HRC and 1600 N/mm ² up to Ø	9 mm
for round steel bar up to 40 HRC and 1200 N/mm ² up to Ø	11 mm
Cutting capacity	<48 HR
with over-expansion guard	yes
Manufacturer's designation	UNIBOLT®
Blade	hardened
Material	Special tool steel

Surface	Painted red
with adjustment screw	yes
Type of product	Cutting pliers

Accessories

Spare jaws complete with screws overall length 910 mm	734110 910
---	------------