

**Carbide universal bit, Drill Ø: 25mm****Order data**

Order number	795250 25
GTIN	9002696014157
Item class	76H

Description**Version:**

Two-edged with cylindrical shank.

With **carbide inserts**; edges stay sharp for long tool life. For drilling in hardwood, plastics, coated panels etc.

Application:

For drilling tear-free and accurate blind holes and through holes.

Standard:

DIN 7483 G

Technical description

Number of cutting edges Z	2
Drill Ø	25 mm
Shank dimension	10×30 mm
overall length	90 mm
Type of product	Wood drill

Accessories

Extension for drill for shank Ø 10 mm	795270 10
---------------------------------------	-----------

