

**Pipe wrench (lighter version), Pipe Ø: 1.1/2in****Order data**

| | |
|--------------|---------------|
| Order number | 810200 1.1/2 |
| GTIN | 4045197166982 |
| Item class | 82A |

Description**Version:**

Swedish design, with broad 90° offset jaw. Fully forged with captive adjustment nut.

Material:

Special tool steel; quenched and tempered, jaws induction hardened.

Technical description

| | |
|---------------------------|-----------------------------------|
| Jaw capacity | 59 mm |
| Pipe Ø | 1.1/2 in |
| overall length | 410 mm |
| Jaw angle | 90 degrees |
| Manufacturing process | forged throughout |
| Hardened and tempered jaw | induction hardened |
| Material of pliers | Special tool steel |
| Type of product | Pipe wrench and water pump pliers |