



Screwdriver for slotted nuts, Blade Ø: 6mm



Order data

Order number	666600 6
GTIN	7610733086375
Item class	63E

Description

Version:

“Classic” power grip of transparent, impact-resistant plastic (cadmium-free). Tubular blade with exceptionally deep head for projecting screw threads.

Application:

For slotted round nuts DIN 546.

Material:

Blade of PB Swiss Tools special alloy, surface nickel-plated and chrome-plated.

Technical description

Drive bit thickness a	1.2 mm
Blade Ø	6 mm
Hole Ø	3.7 mm
overall length	185 mm
for nuts	M3
Blade length	90 mm
Series	Classic
Drive profile	Slotted nut screwdriver
Type of product	Screwdriver