



Chisel and taper pin punch set in a plastic holder special quality, Number of tools: 11



Order data

Order number	745100 11
GTIN	7610733086870
Item class	73B

Description

Version:

Flat and cross-cut chisels for metal, and taper pin punches and centre punches with octagonal shanks, through hardened; chisels can be reground many times. **Head specially annealed** to prevent splintering.

Special quality = Highest possible point hardness – approx. 59 HRC – with exceptional toughness.

Material:

Extra chrome vanadium steel, chrome-plated.

Content:

Centre punch: 1 pc. each size 100×8; 120×10 mm

Taper pin punch: 1 pc. each Ø 2; 4; 5 mm

Flat cold chisel: 1 pc. each 130; 165; 180 mm

Cross-cut cold chisel: 1 pc. each 130; 165 mm

Scriber, double-ended: 1 pc.

Technical description

Number of tools	11
Type of product	Chisels

Accessories

Flat chisel special quality overall length 130 mm	741000 130
Centre punch, special quality, chrome-plated overall length 100 mm	748900 100
Taper pin punches, special quality chrome-plated Tip Ø 4 mm	745300 4
Taper pin punches, special quality chrome-plated Tip Ø 2 mm	745300 2
Flat chisel special quality overall length 180 mm	741000 180
Cross-cut chisel special quality overall length 130 mm	741100 130
Centre punch, special quality, chrome-plated overall length 120/12 mm	748900 120/12
Flat chisel special quality overall length 165 mm	741000 165
Taper pin punches, special quality chrome-plated Tip Ø 5 mm	745300 5
Cross-cut chisel special quality overall length 165 mm	741100 165