



Taper pin punches, special quality chrome-plated, Tip Ø: 5mm



Order data

Order number	745300 5
GTIN	7610733200672
Item class	73B

Description

Version:

Octagonal shank with conical shaft, through hardened. **Head specially annealed** to prevent splintering.

Highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

Material:

Special quality of extra chrome vanadium steel, chrome-plated.

Technical description

overall length	120 mm
Tip Ø	5 mm
Shank Ø	10 mm
Type of product	Drift punch