

**VBW****Corner pipe wrench, Pipe Ø: 1.1/2in****Order data**

Order number	810700 1.1/2
GTIN	4005887271006
Item class	83E

**Description****Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

**VBW** for 3 and 4 point pipe grip. Hexagon nuts and flat components can be gripped securely without deformation. Handles with **non-slip** plastic coating.

**Material:**

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

**Technical description**

overall length	425 mm
Jaw capacity	75 mm
Pipe Ø	1.1/2 in
Jaw angle	45 degrees
Type of handle	coated with non-slip plastic
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

