



Taper pin punch heavy version, Tip Ø: 10mm



Order data

Order number	745500 10
GTIN	4049002002595
Item class	73U

Description

Version:

Octagonal shank with conical shaft, through hardened. **Head specially annealed** to prevent splintering.

Heavy-duty type to DIN 6458 D. **Head annealed.**

Standard:

DIN 6458 D.

Geprüfte Sicherheit nach DIN 7255.

Material:

Standard quality of chrome vanadium steel, shank painted.

Technical description

overall length	150 mm
Tip Ø	10 mm
Shank Ø	12 mm
Weight	150 g
Type of product	Drift punch