



## Corner pipe wrench with quick adjustment, Pipe Ø: 1.1/2in



### Order data

Order number	810750 1.1/2
GTIN	4049002099847
Item class	86A

### Description

#### Version:

Swedish design, with slim 45° offset jaw. Forged throughout. Extremely easy to use, with patented **time-saving quick adjustment** and integral trap protection to avoid pinching fingers. S-form jaws for three-point pipe grip. Handles with **non-slip plastic coating**.

#### Standard:

**DIN 5234**

#### Material:

Chrome vanadium steel; quenched and tempered; jaws induction hardened. Handles painted, jaws bright.

### Technical description

Jaw capacity	60 mm
Pipe Ø	1.1/2 in
overall length	425 mm
Jaw angle	45 degrees
Type of handle	coated with non-slip plastic
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
Standard	DIN 5234
Type of product	Pipe wrench and water pump pliers

