



Corner pipe wrench with quick adjustment, Pipe Ø: 2in



Order data

Order number	810750 2
GTIN	4049002104237
Item class	86A

Description

Version:

Swedish design, with slim 45° offset jaw. Forged throughout. Extremely easy to use, with patented **time-saving quick adjustment** and integral trap protection to avoid pinching fingers. S-form jaws for three-point pipe grip. Handles with **non-slip plastic coating**.

Standard:

DIN 5234

Material:

Chrome vanadium steel; quenched and tempered; jaws induction hardened. Handles painted, jaws bright.

Technical description

overall length	560 mm
Jaw capacity	70 mm
Pipe Ø	2 in
Jaw angle	45 degrees
Type of handle	coated with non-slip plastic
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
Standard	DIN 5234
Type of product	Pipe wrench and water pump pliers

