



Corner pipe wrench with S-form jaws, Pipe Ø: 3in



Order data

Order number	810600 3
GTIN	4045197167071
Item class	82A

Description

Version:

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

HOLEX with **S-form jaws** for 3-point pipe support. (economy version).

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Technical description

Jaw capacity	110 mm
Pipe Ø	3 in
overall length	630 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

Accessories

Knurled nut Type 2

810520 2