



Pipe wrench with movable jaw, for one-handed operation, Pipe Ø: 2in



Order data

Order number	810870 2
GTIN	095691103581
Item class	83R

Description

Version:

Direct and quick positioning using the spring-loaded hook jaw. Handle of sturdy malleable cast iron, red paint finish. Sharp and cleanly finished gripper jaws.

Advantage:

- **Genuine one-handed operation**
- **Smooth ratchet action**
- **Quick and secure grip**

Application:

When tightening, the jaws press tightly on the pipe, and then release automatically when the handle is lifted.

overall length: 350 mm

Jaw capacity: 60 mm

Technical description

Jaw capacity	60 mm
overall length	350 mm
Pipe Ø	2 in
Material of handle	Spheroidal graphite cast iron
Type of product	Pipe wrench and water pump pliers

