



Wire stripping tool chrome-plated VDE insulated, overall length: 160mm



Order data

| | |
|--------------|---------------|
| Order number | 728750 160 |
| GTIN | 4003773021933 |
| Item class | 73F |

Description

Version:

Offset jaws with V-shaped cutting edges (up to max. 5 mm external Ø). Laid-in joint with "no-play" action and opening spring. With adjustable screw for cross section adjustment.

Handles with multi-component covering, **insulated up to 1000V to DIN EN IEC 60900 / VDE 0682-201.**

Jaws chrome-plated.

Material:

Special tool steel, drop-forged and oil-hardened.

Technical description

| | |
|---|---------------------------------|
| overall length | 160 mm |
| Standard | DIN EN IEC 60900 / VDE 0682-201 |
| Cutter form | Vee cutter |
| Handle | Multi-component covering |
| Material | Special tool steel |
| Surface | chrome-plated |
| with return spring | yes |
| with adjustable screw for cross section adjustment. | yes |

Type of product

Cutting pliers