



## Pin punch set in a plastic clip, special quality chrome-plated, Number of pin punches: 6



### Order data

Order number	746910 6
GTIN	7610733014095
Item class	73B

### Description

#### Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual  $\varnothing$  0.05 - 0.5 mm less than nominal  $\varnothing$ , prevents the pin punch jamming in the hole.

**Special quality**, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

#### Material:

Special quality of extra chrome vanadium steel, chrome-plated.

#### Content:

1 each pin punch: 2; 3; 4; 5; 6; 8 mm

### Technical description

Number of pin punches	6
Type of product	Parallel pin punches

---

## Accessories

Pin punch, special qualitychrome-plated Point Ø D 5 mm	746900 5
Pin punch, special qualitychrome-plated Point Ø D 6 mm	746900 6
Pin punch, special qualitychrome-plated Point Ø D 3 mm	746900 3
Pin punch, special qualitychrome-plated Point Ø D 8 mm	746900 8
Pin punch, special qualitychrome-plated Point Ø D 2 mm	746900 2
Pin punch, special qualitychrome-plated Point Ø D 4 mm	746900 4