



Pin punch, special quality powder-coated, Point Ø D: 2mm



Order data

Order number	746920 2
GTIN	7610733243433
Item class	73B

Description

Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

Special quality, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

Material:

Special quality, of extra chrome vanadium steel, chrome-plated and powder-coated.

Technical description

Shank Ø S	10 mm
Point Ø D	2 mm
Mandrel length L2	40 mm
overall length L ₁	150 mm
Point hardness	59 HRC
Material	Special quality of extra chrome vanadium steel
Surface	chrome-plated, powder-coated
Type of product	Parallel pin punches

