

**Pin punch with handle, Tip Ø: 4mm****Order data**

| | |
|--------------|---------------|
| Order number | 746940 4 |
| GTIN | 7610733254910 |
| Item class | 73B |

Description**Version:**

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. Head specially annealed to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

Material:

Special quality extra chrome vanadium steel (i.e. the highest possible peak hardness - approx. 59 HRC - combined with special toughness), chrome-plated. Hand grip with a non-allergenic elastomer coating.

Technical description

| | |
|-----------------------|---|
| Pin length | 67 mm |
| Tip Ø | 4 mm |
| overall length | 175 mm |
| Handle | Plastic handle with skin-friendly elastomer coating |
| Point hardness | 59 HRC |
| Type of striking head | specially annealed |
| Material | Extra chrome vanadium steel, special quality |
| Surface | chrome-plated |
| Type of product | Parallel pin punches |

