

**Centre punch, special quality, chrome-plated, overall length: 120/10mm****Order data**

Order number	748900 120/10
GTIN	7610733200436
Item class	73B

**Description****Version:**

Strong octagonal shank, bright finished point. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering.

**Special quality**, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

**Material:**

Chrome vanadium steel, chrome-plated.

**Technical description**

overall length	120 mm
Shank Ø	10 mm
Point hardness approx.	59 HRC
Type of striking head	annealed
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Centre punches