



Pin punch, special quality chrome-plated, Point Ø D: 8mm



Order data

Order number	746900 8
GTIN	7610733200740
Item class	73B

Description

Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal diameter, prevents the pin punch from jamming in the hole.

Special quality, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

Material:

Special quality of extra chrome vanadium steel, chrome-plated.

Technical description

Point Ø D	8 mm
Shank Ø S	10 mm
overall length L ₁	150 mm
Mandrel length L ₂	45 mm
Point hardness	59 HRC
Material	Special quality of extra chrome vanadium steel
Surface	chrome-plated
Type of product	Parallel pin punches

