



Adjustable spanner with reversible jaw, overall length: 205mm



Order data

Order number	813930 205
GTIN	7314150103447
Item class	83F

Description

Version:

With ergonomic handle of thermoplastic elastomer. Jaw angle 15°. Drop-forged, hardened and chromium plated. By **reversing the rack jaw** the adjustable spanner **becomes a pipe wrench**. The serrated jaw is induction hardened and guarantees a secure grip.

Standard:

ISO 6787; ASME B107.8M-2003

Technical description

overall length	205 mm
maximum width across flats	28 mm
overall length	8 in
Weight	272 g
Standard	ISO 6787
Standard	ASME B107.8M-2003
Jaw position	15 degrees
Manufacturing process	precision hardened, treated for protection against rust
Material	High-performance steel alloy
Surface	chrome-plated
non-sparking	no

Reversible jaws	yes
Scaling	yes
Ratchet function	no
Grips	yes
Type of product	Adjustable spanners