



Pin punch, standard quality, painted, Point Ø D: 3mm



Order data

Order number	747000 3
GTIN	4049002002809
Item class	73U

Description

Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal diameter, prevents the pin punch from jamming in the hole.

Standard:

DIN 6450.

Geprüfte Sicherheit nach DIN 7255.

Material:

Standard quality of chrome vanadium air hardening steel, painted.

Technical description

overall length L ₁	150 mm
Mandrel length L ₂	40 mm
Shank Ø S	10 mm
Point Ø D	3 mm
Standard	DIN 6450 C
Material	Chrome vanadium air hardening steel
Surface	painted
Type of product	Parallel pin punches