

**Pin punch, standard quality, painted, Point Ø D: 4mm****Order data**

Order number	747000 4
GTIN	4049002002823
Item class	73U

**Description****Version:**

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal diameter, prevents the pin punch from jamming in the hole.

**Standard:**

**DIN 6450.**

**Geprüfte Sicherheit nach DIN 7255.**

**Material:**

Standard quality of chrome vanadium air hardening steel, painted.

**Technical description**

Shank Ø S	10 mm
Point Ø D	4 mm
Mandrel length L2	50 mm
overall length L <sub>1</sub>	150 mm
Standard	DIN 6450 C
Material	Chrome vanadium air hardening steel
Surface	painted
Type of product	Parallel pin punches