



Pipe cutter with 3 cutter wheels for steel pipes, for pipes up to: 2in



Order data

Order number	815100 2
GTIN	4018754241910
Item class	83A

Description

Version:

Body of stainless steel drop-forged; wear-resistant spindle with plastic handle. **Cutter wheel** for steel pipes of stainless steel, accurately hardened for long tool life. **Guide rollers** of special steel; chromium-plated.

Application:

For clean and right-angled cutting off of pipes.

This pipe cutter permits work on pipes that have already been laid. A movement range of 120° is sufficient due to ratchet type operation.

Cutter wheel Ø: 41 mm

Cutter wheel width: 19 mm

Cutter wheel bore: 9 mm

for pipe outer Ø: 1/8 – 2 in

Technical description

Cutter wheel bore	9 mm
Cutter wheel width	19 mm
for pipe outer Ø	1/8 – 2 in
Cutter wheel Ø	41 mm
Number of guide rollers	0
Number of cutter wheels	3
Type of product	Pipe cutters

Accessories

Stainless steel inner / outer deburrer for pipe Ø up to 54 mm

814920 54

Stainless steel inner / outer deburrer for pipe Ø up to 54E mm

814920 54E

Stainless steel inner / outer deburrer for pipe Ø up to 35 mm

814920 35

Spare cutter wheel for steel pipes

815250