



Wire stripping side cutter VDE insulated, overall length: 160mm



Order data

Order number	728780 160
GTIN	4003773040279
Item class	73F

Description

Version:

Induction hardened precision cutting edges (approx. 60 HRC) for soft wire. Precision stripping knife for single-core (solid) conductors 1.5 and 2.5 mm². Handles with thick-walled grips **insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000V.**

Application:

Ideal for electrical installation work.

Material:

Special tool steel, jaws chrome-plated, handles with multi-component covering.

Technical description

Cutting capacity soft wire up to Ø	2.5 mm
overall length	160 mm
Wire stripping for conductor Ø	1,5 mm ²
Wire stripping for conductor Ø	2,5 mm ²
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 60 HRC)
Material	Special tool steel
Surface	chrome-plated

Type of product

Cutting pliers