



Installation pliers VDE insulated, overall length: 200mm



Order data

Order number	728787 200
GTIN	4003773075097
Item class	73F

Description

Version:

Multi-function pliers for electrical installation work, with screwed joint for precise, play-free action.

- **For gripping flat and round material.**
- **Bending wires and copper conductors.**
- **Deburring and widening flush-mounted boxes.**
- **Cutting copper cables up to \varnothing 15 mm ($5 \times 2.5 \text{ mm}^2$).**
- **Stripping copper wires 0.75 up to 1.5 mm² and 2.5 mm².**
- **Crimping terminal sleeves 0.5 to 2.5 mm².**

Handles with grips **insulated to DIN EN IEC 60900 / VDE 0682-201.**

Material:

Special tool steel, jaws chrome-plated, handles with multi-component covering.

Technical description

Cutting capacity up to \varnothing	15 mm
overall length	200 mm
Cutting capacity	$5 \times 2.5 \text{ mm}^2$
Wire stripping for conductor \varnothing	0,7 – 1,5 mm ²
Wire stripping for conductor \varnothing	2,5 mm ²
for terminal sleeves	0,5 – 2,5 mm ²
Weight	280 g

Joint	bolted
with return spring	no
Handle	Multi-component covering
Standard	DIN EN IEC 60900 / VDE 0682-201
Material	Special tool steel
Surface	chrome-plated
Type of product	Multi-function pliers