



Centre punch, special quality, chrome-plated Carbide tip, overall length: 120/10mm



Order data

Order number	749300 120/10
GTIN	7610733004669
Item class	73B

Description

Version:

Strong octagonal shank, bright finished point. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering.

Special quality, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

Material:

Chrome vanadium steel, chrome-plated.

With brazed-on **carbide tip**.

Technical description

Shank Ø	10 mm
Point hardness approx.	59 HRC
Type of striking head	annealed
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Centre punches