

RIDGID**Pipe cutter stainless steel (VA) / copper****Order data**

| | |
|--------------|-------------|
| Order number | 819475 |
| GTIN | 95691318039 |
| Item class | 83R |

Description**Version:**

Sturdy design for the heaviest duties and precise cutting using 6 or 12 guide rollers. Extremely quick and low-force operation due to **ball-bearing guide rollers and cutting wheel**. With spare cutter wheel.

Application:

Specially for cutting stainless steel, and galvanised carbon steel pipes (up to 3 mm wall thickness), but also aluminium and copper pipes.

Technical description

| | |
|--------------------|--------------|
| Cutter wheel bore | 8 mm |
| Cutter wheel Ø | 22 mm |
| Cutter wheel width | 8 mm |
| for pipe outer Ø | 6 - 65 mm |
| Type of product | Pipe cutters |

Accessories

| | |
|----------------------------------|--------|
| Ball-bearing roller set 6 pieces | 819479 |
|----------------------------------|--------|

| | |
|--|------------|
| Stainless steel inner / outer deburrer for pipe Ø up to 54E mm | 814920 54E |
| Spare cutter wheels set, 2 pieces | 819480 |
| Set of roller pins 2 pieces | 819478 |
| Stainless steel inner / outer deburrer for pipe Ø up to 54 mm | 814920 54 |
| Stainless steel inner / outer deburrer for pipe Ø up to 35 mm | 814920 35 |
| Wheel pin | 819477 |