



## Electronic torque analyser "ProTest", maximum torque: 400N·m



### Order data

Order number	654460 400
GTIN	5060922231307
Item class	66D

### Description

#### Version:

- **Sturdy cast aluminium body.**
- **Large-format LCD display.**
- **Easy to use – pictogram keypad for direct choice of the test procedure etc.**
- **User-specific input of target torque with upper and lower tolerances; acoustic and visual signal (3 LEDs) on reaching/exceeding the target torque.**
- **3 user modes: Following, inflection point detection, and peak value display.**

#### Advantage:

- **Checking to DIN EN ISO 6789; only the target value has to be put in – the torque analyser does the rest.**
- **11 display languages.**
- **Testing in horizontal and vertical position.**
- **Display and measured value sensor can be separated.**

#### Application:

For setting and calibrating torque tools.

#### Supplied with:

Measured value sensor, display unit, mains adapter, RS-232C connecting cable to PC or printer, 2 securing screws, and square drive adapter all in a sturdy case, **including UKAS calibration certificate, right-hand.**

**Note:**

Wall bracket under No. 654462.

## Technical description

Square drive adapter	3/8 in
Square drive adapter	1/2 in
Square drive adapter	3/4 in
Weight	6.4 kg
Measuring value sensor width	106 mm
Display unit height	128 mm
Measuring value sensor depth	185 mm
Measuring range	8 - 400 Nm
Display unit width	185 mm
maximum torque	400 Nm
Measuring value sensor height	100 mm
Display unit depth	104 mm
Torque measuring accuracy	±0.5 %
Power supply	Mains operated
Direction of tightening	Right-hand tightening
Interface	RS232C interface
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Torque testing device

## Services

Calibration, clockwiseTorque analyser / sensor Type 400	020120 400
DAkkS calibration clockwise / anti-clockwiseTorque analyser / sensor maximum torque 1000/2 N·m	020150 1000/2
DAkkS calibration, clockwiseTorque analyser / sensor Type 1000	020130 1000

---

## Accessories

Wall bracket for ProTest

654462