

**HOLEX**
**HOLEX Pro INOX solid carbide torus cutter HPC DIN 6535 HB, AlCrN, Ø DC / R1:  
8/0,5mm**

**Order data**

Order number	GG1248 8/0,5
GTIN	4045197908773
Item class	GGN

**Description**
**Version:**

Dimensions similar to DIN 6527.

For **outstanding tool life**.

For use at **high cutting speeds, particularly suitable even for steels up to approx. 1100N/mm<sup>2</sup>**.

**Same as No. 206348.**

**Technical description**

Feed $f_z$ for side milling in INOX > 900 N/mm <sup>2</sup>	0.04 mm
Flute length $L_c$	21 mm
Shank	DIN 6535 HB to h6
Corner radius $R_1$	0.5 mm
Overall length $L$	63 mm
Recess $\varnothing D_1$	7.7 mm
Feed $f_z$ for copy milling in stainless steel > 900 N/mm <sup>2</sup>	0.048 mm

Overhang length $L_1$ incl. recess	25 mm
Cutting edge $\varnothing D_c$	8 mm
No. of teeth Z	4
Shank $\varnothing D_s$	8 mm
Helix angle	35 degrees
Contents	5
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	f8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	$0.05 \times D$ for copy milling
Cutting width $a_e$ for milling operation	$0.3 \times D$ for side milling
Machining strategy	HPC
Shank tolerance	h6
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	P

TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	100 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	85 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

## Accessories

HOLEX Pro INOX solid carbide torus cutterHPC DIN 6535  
HB Ø DC / R1 8/0,5 mm

206348 8/0,5