



Dungarees Quality Dress, pale grey, Clothing size DE: 98



Order data

Order number	091132 98
GTIN	4014382988807
Item class	09S

Description

Version:

Quality Dress workwear, 100 % cotton fabric. Cotton is especially resistant to chemical and mechanical influences and also to heat. Cotton is a natural product which is comfortable to wear due to its temperature-regulating properties and high absorbency.

Dungarees with 6 cm waistband adjustment.

- **Sewn-on raised kidney protection.**
- **Open bib patch pocket with hook and loop sub-division.**
- **Double bib with zip fastener pocket.**
- **Impact resistant and heat-resistant plastic buckle.**

Description:

- **Zip fastener in the flies.**
- **Two reinforced front patch pockets.**
- **Thigh pocket.**
- **Mobile phone patch pocket.**
- **Reinforced knee area.**
- **Ruler pocket.**

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Available in other colours on request.

Dungarees in cornflower blue under No. 091131.

Fabric composition: 100% cotton

Material weight/fabric density: 285 g/m²

Clothing standard: UV standard 801

Washing: 60 °C coloureds

Technical description

Plug cap	impact-resistant and heat-resistant plastic buckle
Number of knee pockets	2
Trouser leg end form	straight, open
Mobile phone pocket	yes
reinforced knee area	yes
Kidney protection	yes
Number of side pockets	2
Side pockets	patch, reinforced
Trouser flies	Zip fastener
Clothing size DE	98
Material	Cotton
Bib pocket	patch, with hook and loop sub-division
double bib with zip fastener pocket.	yes
Number of thigh pockets	1
Number of metre rule pockets	1
Size FR	42L
Size UK	34L
Size US	34/34
Size IT	42L
Series	QUALITY DRESS
Special service provision	Textile finishing
Size ES	42L

Size NL	98
Gender	Gentlemen's
Fabric composition	100% cotton
Material weight/fabric density	285 g/m ²
Clothing standard	UV standard 801
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Colour	pale grey
Type of product	Dungarees