

HALDER**MaxxCraft engineer's hammer, Weight without handle: 1000 g****Order data**

| | |
|--------------|---------------|
| Order number | 750550 1000 |
| GTIN | 4030618303084 |
| Item class | 73W |

Description**Version:**

Due to the unique bonding, hammer head and handle sleeve form an inseparable vibration-absorbing unit. Handle protection sleeve with rubber grip. With **hickory handle** ergonomic shape, varnished.

Hammer head drop-forged and ground to size. Carefully hardened and tempered. Head painted, face and peen bright finished.

Advantage:

Perceptible **dead-blow absorption**, thus the full impact force is directed on to the component, allowing non-fatiguing work.

Higher impact force and lower vibration load on the hand than with conventional DIN hammers.

Standard:

Hammerkopf nach **DIN 1041**.

Material:

Special tool steel.

Spare part:

Spare handle available under No. 750555.

Handle length: 310 mm

Technical description

| | |
|----------------------------|-----------|
| Handle length | 310 mm |
| Weight without handle | 1000 g |
| overall length | 360 mm |
| Manufacturer's designation | MAXXCRAFT |
| non-sparking | no |
| Type of product | Hammer |

Accessories

| | |
|--|------------|
| Hickory hammer handle Handle length 310 mm | 750555 310 |
|--|------------|