

## ROLLER

### Pipe-threading tool "Central" complete with sheet metal case, Type: 1/2-114



#### Order data

Order number	820300 1/2-114
GTIN	
Item class	84B

#### Description

##### Version:

Quick cutting head change due to easy insertion into the ratchet head with quick-release lock. Cutting heads with long pipe guide and exactly set threading dies. The dies are particularly wear-resistant and easy to exchange. Ratchet reversible for right- and left-hand threads. The threading dies can be reversed for thread cutting right up to a wall (for short pipe ends that are already in place). Not suitable for stainless steel pipes.

##### Application:

A handy and light die stock for use on building sites. **The small head Ø permits working in confined places.**

##### Suitable for:

BSPT pipe thread to DIN 2999 **taper 1:16.**

##### Content:

Associated cutting heads, 1 pc. each (for Whitworth pipe threads): 1/2; 3/4; 1; 1.1/4 inch;  
Ratchet arm: 1 pc.

##### Note:

The following items are also available as individual parts on request:

- **Ratchet arm No. 820600**
- **Sheet metal case No. 820620**
- **Complete cutting heads with jaws No. 820650 and spare jaws No. 820670.**

When ordering please state the desired size.

## Technical description

Number of ratchet arms	1
Whitworth pipe threading head	1/2; 3/4; 1; 1.1/4 in
Standard	DIN EN 10226
Packaging	Sheet metal case
Type of product	Pipe-threading tool

## Accessories

Carrying box of sheet steel for pipe-threading tool "Central" Type C1.1/4	820620 C1.1/4
Cutting head with jaws Thread type R1	820650 R1
Cutting head with jaws Thread type R1.1/4	820650 R1.1/4
Cutting head with jaws Thread type R3/4	820650 R3/4