



One-hand pipe bending pliers with 4 bending segments, Type: 2



Order data

Order number	821100 2
GTIN	4004625241325
Item class	86B

Description

Version:

Pipe bending pliers in sheet metal design with gear rack mechanism. Bending formers and counter plate are fastened by slipping on. For each pipe \varnothing an individual bending former or reaction plate is required.

Application:

For **copper** and **aluminium** pipes from 5 to 12 mm \varnothing as well as for **thin-walled soft steel pipes** from 5 to 10 mm \varnothing . Bending angles up to 90°.

Content:

1 each bending segment for pipes with external \varnothing : 6; 8; 10 and 12 mm

Counter plate No. 821135: 1 pc.

Pipe bending pliers No. 821145: 1 pc.

Plastic case LxWxH: 260x245x85 mm

Note:

Reaction plate No. 821135 and pipe bending pliers No. 821145 and the suitable bending segment are also available individually upon request.

Technical description

Number of bending segments	4
----------------------------	---

Number of pipe bending pliers	1
Number of reaction plates	1

Accessories

One-hand pipe bending pliers without bending set	821145
Bending segment for No. 821145 Type 8	821125 8
Reaction plate for No. 821145	821135
Bending segment for No. 821145 Type 10	821125 10
Bending segment for No. 821145 Type 6	821125 6
Bending segment for No. 821145 Type 12	821125 12