

CoolSpeed®**High-speed spindle housing, Type: TB90****Order data**

Order number	319991 TB90
GTIN	4045197911476
Item class	36D

Description**Version:**

High-speed spindle, driven by coolant (10 – 60 bar), speeds up to 75,000 rpm.

Application:

Increased feed rate and cutting speed, for use above all with small-diameter tools (shank \varnothing 3 – 6 mm). For use for drilling, deburring, engraving, and milling to a restricted degree.

Technical description

External \varnothing D	16 mm
External \varnothing D ₁	25.5 mm
Shank length L ₁	13.5 mm
\varnothing D ₂	25 mm
L ₂	40 mm
L ₃	70 mm
Type of product	High-speed spindle