

**CoolSpeed®****High-speed spindle housing, Type: TB****Order data**

Order number	319991 TB
GTIN	4045197911469
Item class	36D

**Description****Version:**

High-speed spindle, driven by coolant (10 – 60 bar), speeds up to 75,000 rpm.

**Application:**

Increased feed rate and cutting speed, for use above all with small-diameter tools (shank  $\varnothing$  3 – 6 mm). For use for drilling, deburring, engraving, and milling to a restricted degree.

**Technical description**

External $\varnothing$ D	25 mm
Shank length L <sub>1</sub>	10 mm
External $\varnothing$ D <sub>1</sub>	25.5 mm
L <sub>2</sub>	30 mm
Type of product	High-speed spindle