



Water-tight case "Explorer", Type: 5822



Order data

Order number	692930 5822
GTIN	8024482008721
Item class	64A

Description

Version:

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C. Heavenly Delight versions with a weight saving of approx. 30% and increased strength compared to previous models.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For protection, packaging, and transport of delicate parts and devices.

Note:

Many other case sizes, fittings variants, and accessories available on request.

Technical description

Internal dimension width	440 mm
External dimension width	510 mm

Volume	56.1 l
Number of side handles	2
Internal dimension height	220 mm
maximum loading	36.7 kg
Internal dimension length	580 mm
Number of catches	4
External dimension height	245 mm
External dimension length	650 mm
Weight	8.4 kg
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system