



Water-tight case "Explorer", Type: 5833



Order data

Order number	692930 5833
GTIN	8024482008769
Item class	64A

Description

Version:

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For protection, packaging, and transport of delicate parts and devices.

Note:

Many other case sizes, fittings variants, and accessories available on request.

Technical description

maximum loading	62 kg
Number of wheels	2
Weight	12.7 kg

Number of side handles	2
External dimension length	670 mm
Number of catches	4
Internal dimension width	440 mm
Volume	84.2 l
Internal dimension length	580 mm
External dimension height	372 mm
External dimension width	510 mm
Internal dimension height	330 mm
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system