

 **HALDER**
**SIMPLEX soft-faced hammer with plastic inserts, red, Body Ø / Material:  
40Amm**

**Order data**

Order number	752900 40A
GTIN	4030618300458
Item class	73W

**Description**
**Version:**

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

**Soft-faced hammers and driving mallets:** Aluminium or annealed cast iron housing; wooden handle.

**Application:**

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

**Spare part:**

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

**Note:**

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing. No soft metal inserts (Ho No. 754000) may be mounted in an aluminium housing.

**Technical description**

Weight	0.39 kg
Head length with inserts	110 mm
Material of the handle	wood
Overall length	330 mm

Handle length	280 mm
Striking face Ø of the inserts	40 mm
Material of body	Aluminium
Series	SIMPLEX soft-faced hammer
Material of insert	Plastic, hard
Manufacturer's designation	SIMPLEX
Colour	red
Type of product	Hammer

## Accessories

SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 40 mm	753700 40
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 40 mm	753450 40
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 40G mm	753310 40G
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 40 mm	753600 40
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 40 mm	753500 40
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 40A mm	753310 40A
SIMPLEX soft-faced hammer, spare handle for body Ø 40 mm	753400 40
SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 40 mm	754000 40