



Dungarees Quality Dress, pale grey, Clothing size DE: 50



Order data

Order number	091132 50
GTIN	4014382988708
Item class	09S

Description

Version:

Quality Dress workwear, 100 % cotton fabric. Cotton is especially resistant to chemical and mechanical influences and also to heat. Cotton is a natural product which is comfortable to wear due to its temperature-regulating properties and high absorbency.

Dungarees with 6 cm waistband adjustment.

- **Sewn-on raised kidney protection.**
- **Open bib patch pocket with hook and loop sub-division.**
- **Double bib with zip fastener pocket.**
- **Impact resistant and heat-resistant plastic buckle.**

Description:

- **Zip fastener in the flies.**
- **Two reinforced front patch pockets.**
- **Thigh pocket.**
- **Mobile phone patch pocket.**
- **Reinforced knee area.**
- **Ruler pocket.**

Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Available in other colours on request.

Dungarees in cornflower blue under No. 091131.

Fabric composition: 100% cotton

Material weight/fabric density: 285 g/m²

Clothing standard: UV standard 801

Washing: 60 °C coloureds

Technical description

Side pockets	patch, reinforced
Trouser leg end form	straight, open
Kidney protection	yes
Number of side pockets	2
Number of metre rule pockets	1
Trouser flies	Zip fastener
Mobile phone pocket	yes
Bib pocket	patch, with hook and loop sub-division
reinforced knee area	yes
Number of thigh pockets	1
Clothing size DE	50
double bib with zip fastener pocket.	yes
Number of knee pockets	2
Material	Cotton
Plug cap	impact-resistant and heat-resistant plastic buckle
Size FR	44
Unisex size	M
Size UK	34R
Size US	34/32
Size IT	44
Series	QUALITY DRESS
Special service provision	Textile finishing

Size ES	44
Size NL	50
Gender	Gentlemen's
Fabric composition	100% cotton
Material weight/fabric density	285 g/m ²
Clothing standard	UV standard 801
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Colour	pale grey
Type of product	Dungarees