

 **HALDER**
**SIMPLEX soft-faced hammer without inserts, with handle, Body Ø / Material: 30Gmm**

**Order data**

Order number	753300 30G
GTIN	2050001008404
Item class	73W

**Description**
**Version:**

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

**Soft mallets and driving mallets:** Aluminium or annealed cast iron housing; wooden handle.

**Soft-faced hammers and driving mallets:** Aluminium or annealed cast iron housing; wooden handle.

**Application:**

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

**Spare part:**

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

**Note:**

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

**Technical description**

Handle length	260 mm
Striking face Ø of the inserts	30 mm
Material of body	Cast steel
Body Ø	30 mm
Head length with inserts	90 mm

Overall length	300 mm
Series	SIMPLEX soft-faced hammer
Type of product	Soft-faced hammer housing

## Accessories

SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 30 mm	753450 30
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 30 mm	753500 30
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 30 mm	753700 30
SIMPLEX soft-faced hammer, spare handle for body Ø 30 mm	753400 30
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 30 mm	753600 30
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 30G mm	753310 30G