

 **HALDER**
**SIMPLEX soft-faced hammer with composite rubber inserts, black, Body Ø /
Material: 30Gmm**


Order data

Order number	752800 30G
GTIN	4030618300045
Item class	73W

Description

Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Material of the handle	wood
Weight	0.345 kg
Striking face Ø of the inserts	30 mm
Overall length	300 mm
Head length with inserts	90 mm

Material of body	Cast steel
Handle length	260 mm
Series	SIMPLEX soft-faced hammer
Material of insert	Rubber composition, medium hard
Manufacturer's designation	SIMPLEX
Colour	black
Type of product	Hammer

Accessories

SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 30 mm	753600 30
SIMPLEX soft-faced hammer, spare handle for body Ø 30 mm	753400 30
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 30G mm	753310 30G
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 30 mm	753500 30
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 30 mm	753700 30
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 30 mm	753450 30