

 **HALDER**
**SIMPLEX soft-faced hammer with plastic inserts, red, Body Ø / Material:
50Amm**

Order data

Order number	752900 50A
GTIN	4030618300465
Item class	73W

Description
Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing. No soft metal inserts (Ho No. 754000) may be mounted in an aluminium housing.

Technical description

Overall length	365 mm
Weight	0.72 kg
Handle length	310 mm
Striking face Ø of the inserts	50 mm

Material of body	Aluminium
Material of the handle	wood
Head length with inserts	135 mm
Series	SIMPLEX soft-faced hammer
Material of insert	Plastic, hard
Manufacturer's designation	SIMPLEX
Colour	red
Type of product	Hammer

Accessories

SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 50 mm	753500 50
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 50G mm	753310 50G
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 50 mm	753450 50
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 50 mm	753600 50
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 50 mm	753700 50
SIMPLEX soft-faced hammer, spare handle for body Ø 50 mm	753400 50
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 50A mm	753310 50A
SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 50 mm	754000 50