

 **HALDER**
**SIMPLEX soft-faced hammer with super-plastic inserts, white, Body Ø /  
Material: 100Gmm**


## Order data

Order number	753100 100G
GTIN	4030618300861
Item class	73W

## Description

**Version:**

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

**Soft-faced hammers and driving mallets:** Aluminium or annealed cast iron housing; wooden handle. **Sledgehammers:** Annealed cast iron housing; American hickory wood handle.

**Application:**

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

**Spare part:**

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

**Note:**

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

## Technical description

Weight	5.2 kg
Material of the handle	Hickory
Handle length	900 mm
Head length with inserts	200 mm
Striking face Ø of the inserts	100 mm
Overall length	1000 mm

Material of body	Cast steel
Series	SIMPLEX soft-faced hammer
Material of insert	Super-plastic, medium hard
Manufacturer's designation	SIMPLEX
Colour	white
Type of product	Hammer

## Accessories

SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 100 mm	753700 100
SIMPLEX soft-faced hammer, spare handle for body Ø 100-125 mm	753400 100-125