#### **A HALDER**

# SIMPLEX soft-faced hammer with plastic inserts, red, Body $\varnothing$ / Material: 50Gmm



### **Order data**

Order number	752900 50G
GTIN	4030618300151
Item class	73W

## **Description**

#### **Version:**

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

**Soft-faced hammers and driving mallets:** Aluminium or annealed cast iron housing; wooden handle.

#### **Application:**

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

#### **Spare part:**

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

#### Note:

Size codes  $\mathbf{A}$  = Aluminium housing;  $\mathbf{G}$  = Annealed cast iron housing.

## **Technical description**

Overall length	365 mm
Striking face Ø of the inserts	50 mm
Handle length	310 mm
Material of body	Cast steel
Head length with inserts	135 mm

Weight	1.12 kg
Material of the handle	wood
Series	SIMPLEX soft-faced hammer
Material of insert	Plastic, hard
Manufacturer's designation	SIMPLEX
Colour	red
Type of product	Hammer

## **Accessories**

SIMPLEX soft-faced hammer, rubber composition insert for Hammer head $\varnothing$ 50 mm	753500 50
SIMPLEX soft-faced hammer housing without inserts, without handle for body $\varnothing$ / material 50G mm	753310 50G
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 50 mm	753600 50
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head $\varnothing$ 50 mm	753450 50
SIMPLEX soft-faced hammer, soft metal insert for Hammer head $\varnothing$ 50 mm	754000 50
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head $\varnothing$ 50 mm	753700 50
SIMPLEX soft-faced hammer, spare handle for body Ø 50 mm	753400 50
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 50A mm	753310 50A