

 **HALDER**
**SIMPLEX soft-faced hammer with super-plastic inserts, white, Body Ø /
Material: 125Gmm**


Order data

Order number	753100 125G
GTIN	4030618300878
Item class	73W

Description

Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle. **Sledgehammers:** Annealed cast iron housing; American hickory wood handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Overall length	1050 mm
Striking face Ø of the inserts	125 mm
Material of the handle	Hickory
Head length with inserts	215 mm
Material of body	Cast steel
Handle length	900 mm

Weight	7.7 kg
Series	SIMPLEX soft-faced hammer
Material of insert	Super-plastic, medium hard
Manufacturer's designation	SIMPLEX
Colour	white
Type of product	Hammer

Accessories

SIMPLEX soft-faced hammer, spare handle for body Ø 100-125 mm	753400 100-125
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 125 mm	753700 125